

YAV300M10

by Burndy
Catalog ID: YAV300M10

Compression terminal Hylug Copper tubing; 1 Hole; 300 mm²; M10 Stud;
Tin Plating



Product Details

General

Die Index	22
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637531
UPC 12 Digit	7818106375311

Dimensions

Bolt Size	M10
Dimension - B Length inch	0.38 in
Dimension - L Length Overall mm	7 mm
Dimension - Length Overall inch	0.27 in
Dimension - Pad Width inch	0.74 in
Dimension - Strip Length inch	1.38 in
Dimension - Z inch	0.42 in
Thickness - Pad	0.27 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 mm ² ,600 AWG
-----------------------------	------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)