

YAV300M12

by Burndy
Catalog ID: YAV300M12

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W,
300mmClass2, 1/2" stud, Tin - Electro Plated, 22 Index



Product Details

General

Connector Type	Terminal
Die Index	22
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810311004
UPC 12 Digit	7818103110044

Dimensions

Bolt Size	M12
Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	0.38 in
Dimension - Bolt Hole Size inch	0.22 in
Dimension - Bolt Size fraction	#12
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - Inside Diameter inch	0.92 in
Dimension - L Length Overall mm	7 mm
Dimension - Length Overall inch	0.26 in
Dimension - N inch	0.54 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	0.74 in
Dimension - Strip Length inch	1.38 in
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.26 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 mm ² ,600 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)