

YAV352M10

by Burndy
Catalog ID: YAV352M10

Non insulated Cu tubular terminals, Metric, 2 Holes/W/insp W,
35mmClass2,5, 3/8" stud, Tin - Electro Plated, 10 Index



Product Details

General

Die Index	10
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810636503
UPC 12 Digit	7818106365033

Dimensions

Bolt Size	M10
Dimension - B Length inch	16.0 in
Dimension - L Length Overall mm	91 mm
Dimension - Length Overall inch	3.57 in
Dimension - N inch	0.41 in
Dimension - Pad Width inch	17.3 in
Dimension - Strip Length inch	0.67 in
Dimension - Z inch	0.42 in
Thickness - Pad	0.10 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	35 mm ² , 2 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)