

# YAV352M6

by Burndy  
Catalog ID: YAV352M6

Hylug Copper tubing Compression terminals, 35 mm<sup>2</sup>, M6 Stud, 2 Holes, Tin Plated



## Product Details

### General

Die Index	10
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637821
UPC 12 Digit	7818106378211

### Dimensions

Bolt Size	M6
Dimension - B Length inch	16.0 in
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.45 in
Dimension - N inch	0.34 in
Dimension - Pad Width inch	17.3 in
Dimension - Strip Length inch	0.67 in
Dimension - Z inch	0.33 in
Thickness - Pad	0.10 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	35 mm <sup>2</sup> , 2 AWG
-----------------------------	----------------------------

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)