

# YAV400FM12

by Burndy  
Catalog ID: YAV400FM12

Non insulated Cu tubular terminals, Metric, 1 Hole/W/Insp W, 400 mm Class 2, M12 stud. Tin plated. 24 Index



## Product Details

### General

Connector Type	Terminal
Die Index	24
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323472
UPC 12 Digit	7818103234722

### Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.22 in
Dimension - Bolt Size fraction	#12
Dimension - D inch	1.14 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - Inside Diameter inch	1.07 in
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.43 in
Dimension - N inch	0.57 in
Dimension - Outside Diameter inch	1.38 in
Dimension - Pad Width inch	1.98 in
Dimension - Strip Length inch	1.46 in
Dimension - Z inch	0.55 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	650
Conductor - Copper Str Size Range	650
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)