

# YAV400FM14

by Burndy  
Catalog ID: YAV400FM14

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 400 mm, 14 mm Stud, 3.47 IN L, Compression, 24 Index, 37 mm Strip Length



## Product Details

### General

Connector Type	Terminal
Die Index	24
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Metric Terminals
UPC	781810323496
UPC 12 Digit	7818103234966

### Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	#14
Dimension - Hole Size inch	0.59 in
Dimension - Hole Size mm	15 mm
Dimension - Inside Diameter inch	1.07 in
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.90 in
Dimension - N inch	0.61 in
Dimension - Outside Diameter inch	1.38 in
Dimension - Pad Width inch	1.98 in
Dimension - Strip Length inch	1.46 in
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)