

YAV400M20

by Burndy
Catalog ID: YAV400M20

Copper Tubing Terminal, 1 Hole W/insp window, 400 mm Class 2, 24 Index, M20 Stud



Product Details

General

Connector Type	Terminal
Die Index	24
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323557
UPC 12 Digit	7818103235577

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	0.42 in
Dimension - D inch	1.81 in
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - Inside Diameter inch	1.05 in
Dimension - L Length Overall mm	8 mm
Dimension - Length Overall inch	0.30 in
Dimension - N inch	0.88 in
Dimension - Pad Width inch	0.98 in
Dimension - Strip Length inch	1.46 in
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)