

YAV4/OT12B

by Burndy
Catalog ID: YAV4/OT12B

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 4/0 Flex, 1/2" Stud, Short Barrel, Belled End, Tin Plated



Product Details

General

Can be mounted up or down	No
Category General	Outdoor
Color	Black
Color Generic	black
Connector Type	Terminal
Construction Material - Main	Aluminum
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Glass	Clear Heat Strengthened Double Strength
Lamp Included	No
Lamp Type Basic	accessories
Material	Copper
Mount location	Wall
Mounting for outlet box included	No
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Prewired	No
Quick Install canopy	No
Quick Link connector	No
Style	Utilitarian/Commodity
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated

UPC	785247879700 781810425640
UPC 12 Digit	7818104256400

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.08 in
Dimension - L Length Overall mm	61 mm
Dimension - Length Overall inch	2.39 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.10 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.55 in
Gross Weight with Packaging	0.7 lb
Height	0.75 in
Physical Attribute - Tongue Angle	Straight
Weight	0.7 lb
Width	6 in
Width Diameter Descriptor	W.

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Flex M Size Range	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Americans with Disabilities Act	No
Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
DarkSky	No
ENERGY STAR Certified	No
Energy Efficient	No
EnergyStar	No
JA8	No
Other Heavy Metal Content Indicator	No
Standards - RoHS Compliance Status	CM
Title 20	No
Title 22	No
Title 24	No
UL Listed	No

Logistics

Carton Quantity	3 EA
Minimum Pack Quantity	10

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)