

## YAV444T58B

by Burndy  
Catalog ID: YAV444T58B

Copper Compression Lug, 1 Hole w/ Inspection Window, 444 Flex, 5/8" Stud, Short Barrel, Belled End, Tin Plated



### Product Details

#### General

Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	621945082441
UPC 12 Digit	6219450824411

#### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - D inch	1.72 in
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.68 in
Dimension - N inch	0.85 in
Dimension - Outside Diameter inch	1.18 in
Dimension - Pad Width inch	1.69 in

Dimension - Thread Size	5/8 in
Dimension - Z inch	0.87 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex G Size	444
Conductor - Copper Flex G Size Range	444
Conductor - Copper Flex H Size	444
Conductor - Copper Flex H Size Range	444
Conductor - Copper Flex I Size	444
Conductor - Copper Flex I Size Range	444
Conductor - Copper Flex K Size	444
Conductor - Copper Flex K Size Range	444
Conductor - Copper Flex M Size	444
Conductor - Copper Flex M Size Range	444
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)