

YAV5002M20

by Burndy
Catalog ID: YAV5002M20

Hylug Copper tubing Compression terminals,500 mm²,M20 Stud, 2 Holes,Tin Plated



Product Details

General

Die Index	L115
Material	Copper
Plated	yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638019
UPC 12 Digit	7818106380199

Dimensions

Dimension - B Length inch	1.65 in
Dimension - L Length Overall mm	160 mm
Dimension - Length Overall inch	6.24 in
Dimension - Pad Width inch	55.6 in
Dimension - Strip Length inch	1.69 in
Dimension - Z inch	0.89 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)