

## YAV500F2M16

by Burndy  
Catalog ID: YAV500F2M16

Cu Compression Lug, 2 Hole, W/Inspection Window, 500 mm, M16 Stud,  
44.5 mm Spacing, Standard Barrel, 41.9 mm Wire Strip Length



### Product Details

#### General

|              |                      |
|--------------|----------------------|
| Die Index    | L115                 |
| Material     | Copper               |
| Plated       | yes                  |
| Plating Type | Tin - Electro Plated |
| Trade Name   | HYLUG™               |
| Type         | Metric Terminals     |
| UPC          | 781810641156         |
| UPC 12 Digit | 7818106411566        |

#### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length inch       | 1.65 in |
| Dimension - Length Overall inch | 5.80 in |
| Dimension - Pad Width inch      | 2.19 in |
| Dimension - Strip Length inch   | 1.69 in |
| Dimension - Z inch              | 0.67 in |

#### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

#### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | CM |

#### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)