

# YAV500F2M20

by Burndy  
Catalog ID: YAV500F2M20

Cu Compression Lug, 2 Hole, W/Inspection Window, 500 mm, M20 Stud, 44.5 mm Spacing, Standard Barrel, 41.9 mm Wire Strip Length



## Product Details

### General

Die Index	L115
Material	Copper
Plated	yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641163
UPC 12 Digit	7818106411633

### Dimensions

Dimension - B Length inch	1.65 in
Dimension - L Length Overall mm	158.4
Dimension - Length Overall inch	6.24 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	1.69 in
Dimension - Z inch	0.89 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)