

# YAV500M20

by Burndy  
Catalog ID: YAV500M20

Copper Tubing Terminal, 1 Hole W/insp window, 500 mm Class 2, L115 Index, 20 mm Stud



## Product Details

### General

Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323687
UPC 12 Digit	7818103236877

### Dimensions

Dimension - B Length fraction	2-3/16 in
Dimension - B Length inch	0.65 in
Dimension - D inch	1.81 in
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - Inside Diameter inch	1.17 in
Dimension - L Length Overall mm	8 mm
Dimension - Length Overall inch	0.33 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	0.19 in
Dimension - Strip Length inch	1.69 in
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)