

YAV502M14

by Burndy
Catalog ID: YAV502M14

HYLUG™ Copper tubing Compression terminals, 50 mm, M14 Stud, 2 Holes, Tin Plated



Product Details

General

Die Index	12
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637883
UPC 12 Digit	7818106378833

Dimensions

Dimension - B Length inch	16.0 in
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.86 in
Dimension - Pad Width inch	21.1 in
Dimension - Strip Length inch	0.67 in
Dimension - Z inch	0.57 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)