

YAV50F2M14

by Burndy
Catalog ID: YAV50F2M14

Cu Compression Lug, 2 Hole, W/Inspection Window, 50 mm, M14 Stud,
44.5 mm Spacing, Standard Barrel, 19 mm Wire Strip Length



Product Details

General

Die Index	12
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810640678
UPC 12 Digit	7818106406788

Dimensions

Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.59 in
Dimension - L Length Overall mm	101.3 mm
Dimension - Length Overall inch	3.99 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	0.69 in
Dimension - Z inch	0.57 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)