

## YAV50F2M6

by Burndy  
Catalog ID: YAV50F2M6

Cu Compression Lug, 2 Hole, W/Inspection Window, 50 mm<sup>2</sup>, M8 Stud, 44.5 mm Spacing, Standard Barrel, 19 mm Wire Strip Length



### Product Details

#### General

|              |                      |
|--------------|----------------------|
| Die Index    | 12                   |
| Material     | Copper               |
| Plated       | Yes                  |
| Plating Type | Tin - Electro Plated |
| Trade Name   | HYLUG™               |
| Type         | Metric Terminals     |
| UPC          | 781810640630         |
| UPC 12 Digit | 7818106406300        |

#### Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - B Length inch         | 0.69 in |
| Dimension - Bolt Hole Size inch   | 0.27 in |
| Dimension - L Length Overall mm   | 89.2mm  |
| Dimension - Length Overall inch   | 3.51 in |
| Dimension - N inch                | 0.31 in |
| Dimension - Outside Diameter inch | 0.56 in |
| Dimension - Pad Width inch        | 0.83 in |
| Dimension - Strip Length inch     | 0.69 in |
| Dimension - Z inch                | 0.33 in |

#### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

#### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | CM |

## Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 20 |
|-----------------------|----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)