

# YAV50FM12

by Burndy  
Catalog ID: YAV50FM12

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 50 mm, M12 Stud, 2.19 IN L, Compression, 12 Index, 19 mm Strip Length



## Product Details

### General

Connector Type	Terminal
Die Index	12
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810243121
UPC 12 Digit	7818102431211

### Dimensions

Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.53 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	55.6mm
Dimension - Length Overall inch	2.19 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	0.69 in
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	50 EA
Minimum Pack Quantity	20

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)