

YAV50FM14

by Burndy
Catalog ID: YAV50FM14

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 50 mm, M14 Stud, 2.23 IN L, Compression, 12 Index, 19 mm Strip Length



Product Details

General

Connector Type	Terminal
Die Index	12
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323700
UPC 12 Digit	7818103237000

Dimensions

Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.59 in
Dimension - Bolt Size fraction	#14
Dimension - Hole Size fraction	3/5
Dimension - Hole Size inch	0.59 in
Dimension - Hole Size mm	15 mm
Dimension - L Length Overall mm	56.6mm
Dimension - Length Overall inch	2.23 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	0.69 in
Dimension - Stud Size inch	#14
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	50
Conductor - Copper Flex H Size	50
Conductor - Copper Flex I Size	50
Conductor - Copper Flex K Size	50
Conductor - Copper Flex M Size	50

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)