

YAV50M16

by Burndy
Catalog ID: YAV50M16

Copper Tubing Terminal, 1 Hole W/insp window, 50 mm Class 2, 12 Index, 16 mm Stud



Product Details

General

Connector Type	Terminal
Die Index	12
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323762
UPC 12 Digit	7818103237622

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.63 in
Dimension - D inch	1.24 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - Inside Diameter inch	0.36 in
Dimension - L Length Overall mm	4 mm
Dimension - Length Overall inch	0.14 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.02 in
Dimension - Strip Length inch	0.67 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)