

YAV630F2M12

by Burndy
Catalog ID: YAV630F2M12

Cu Compression Metric Lug Terminal, 2 Holes W/InspWindow, 630 mm², M12 Stud



Product Details

General

| | |
|--------------|----------------------|
| Die Index | 31 |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Metric Terminals |
| UPC | 781810643020 |
| UPC 12 Digit | 7818106430200 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 2 |
| Dimension - L Length Overall mm | 155 mm |
| Dimension - Length Overall inch | 6.10 in |
| Dimension - Pad Width inch | 2.69 |
| Dimension - Strip Length inch | 2.17 in |
| Dimension - Z inch | 0.55 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------|---------------------|
| Conductor - Copper Str Size | 630 mm ² |
|-----------------------------|---------------------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 2 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)