

YAV630M16

by Burndy
Catalog ID: YAV630M16

Copper Tubing Terminal, 1 Hole W/insp window, 630 mm Class 2, 29 Index, 16 mm Stud



Product Details

General

Connector Type	Terminal
Die Index	29
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810286562
UPC 12 Digit	7818102865622

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - D inch	1.38 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	17.5mm
Dimension - L Length Overall mm	114mm
Dimension - Length Overall inch	4.49 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.69 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	2.17 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)