

YAV630M20

by Burndy
Catalog ID: YAV630M20

Copper Tubing Terminal, 1 Hole W/insp window, 630 mm Class 2, 29 Index, 20 mm Stud



Product Details

General

Connector Type	Terminal
Die Index	29
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323830
UPC 12 Digit	7818103238300

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Hole Size inch	0.94 in
Dimension - Hole Size mm	23.8mm
Dimension - L Length Overall mm	125.2mm
Dimension - Length Overall inch	0.38 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.69 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	2.17 in
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)