

# YAV702M12

by Burndy  
Catalog ID: YAV702M12

HYLUG™ Copper tubing Compression terminals, Metric, 2 Holes With Inspection Window, 70mm² Class2, M12 stud, Tin - Electro Plated



## Product Details

### General

Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637920
UPC 12 Digit	7818106379200

### Dimensions

Dimension - B Length inch	0.69 in
Dimension - Hole Size inch	0.53 in
Dimension - L Length Overall mm	100 mm
Dimension - Length Overall inch	3.95 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	0.748 in
Dimension - Stud Size inch	M12
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	70 mm <sup>2</sup> (1/0 AWG)
Conductor - Copper Str Size Range	70 mm <sup>2</sup> (1/0 AWG)
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)