

# YAV70F2M14

by Burndy  
Catalog ID: YAV70F2M14

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 70 mm<sup>2</sup>  
CLASS 5, M14 Stud, 44.5 mm Spacing, Standard Barrel, 22 mm Wire Strip Length



## Product Details

### General

Connector Type	Terminal
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810640739
UPC 12 Digit	7818106407399

### Dimensions

Dimension - B Length inch	0.81 in
Dimension - Hole Size inch	0.59 in
Dimension - L Length Overall mm	106 mm
Dimension - Length Overall inch	4.16 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	0.866 in
Dimension - Stud Size inch	M14
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	70 mm <sup>2</sup> (1/0 AWG)
Conductor - Copper Str Size Range	70 mm <sup>2</sup> (1/0 AWG)
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)