

YAV70F2M16

by Burndy
Catalog ID: YAV70F2M16

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 70 mm²
CLASS 5, M16 Stud, 44.5 mm Spacing, Standard Barrel, 22 mm Wire Strip Length



Product Details

General

Connector Type	Terminal
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810640746
UPC 12 Digit	7818106407466

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Hole Size inch	0.69 in
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.37 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	0.866 in
Dimension - Stud Size inch	M16
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	70 mm ² (1/0 AWG)
Conductor - Copper Str Size Range	70 mm ² (1/0 AWG)
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)