

# YAV70FM6

by Burndy  
Catalog ID: YAV70FM6

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 70 mm, 6 mm Stud, 1.92 IN L, Compression, 13 Index, 22 mm Strip Length



## Product Details

### General

Connector Type	Terminal - Ring
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Type	Metric Terminals
UPC	781810323991

### Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	0.81 in
Dimension - Hole Size inch	0.25 in
Dimension - Length Overall inch	1.92 in
Dimension - N inch	0.30 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	0.87 in
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	1/0 AWG
-----------------------------	---------

### Certifications and Compliance

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

100
-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)