

# YAV70M10

by Burndy  
Catalog ID: YAV70M10

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W,  
70mmClass2, 3/8" stud, Tin - Electro Plated

Features:One hole hylug code conductor standard barrel



## Product Details

### General

Application	Metric Conductor with Window Lug
Connector Type	Terminal - Ring
Construction Material - Main	Copper tubing
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	Terminals, HYLUG
Trade Name	HYLUG™
Type	YAV
UPC	781810328200

### Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.69 in
Dimension - Hole Size inch	0.41 in
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.39 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	0.75 in
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Str Size	1/0
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	20
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)