

YAV70M14

by Burndy
Catalog ID: YAV70M14

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 70 mm, 14 mm Stud, 2.23 IN L, Compression, 13 Index, 19 mm Strip Length



Product Details

General

Connector Type	Terminal - Ring
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810324011

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.69 in
Dimension - Hole Size inch	0.59 in
Dimension - Length Overall inch	2.23 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	0.75 in
Dimension - Stud Size inch	#14
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1/0 AWG
-----------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)