

YAV777T58B

by Burndy
Catalog ID: YAV777T58B

Copper Compression Lug, 1 Hole w/ Inspection Hole, 777.7 Flex, 5/8" Stud, Short Barrel, Belled End, Tin Plated



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	621945082496

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Length Overall inch	4.82 in
Dimension - N inch	0.94 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	2.19 in
Dimension - Z inch	1.18 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	777
Conductor - Copper Flex H Size	777
Conductor - Copper Flex I Size	777

Conductor - Copper Flex K Size	777
Conductor - Copper Flex M Size	777
Conductor - Copper Flex M Size Range	777
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)