

# YAV95FM14

by Burndy  
Catalog ID: YAV95FM14

Copper Tubing Terminal, 1 Hole W/insp window, 95 mm Class 5, 14 Index, 14 mm Stud



## Product Details

### General

Connector Type	Terminal - Ring
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810324080
UPC 12 Digit	7818103240800

### Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - D inch	1.12 in
Dimension - Hole Size inch	0.59 in
Dimension - Hole Size mm	15 mm
Dimension - Inside Diameter inch	0.56 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.63 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1.06 in
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	2/0 AWG
-----------------------------	---------

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)