

YAV95M12

by Burndy
Catalog ID: YAV95M12

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W,
95mmClass2, M12 stud, Tin - Electro Plated, 14 Index



Product Details

General

Connector Type	Terminal
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810237540
UPC 12 Digit	7818102375400

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5
Dimension - L Length Overall mm	59.9
Dimension - Length Overall inch	2.36
Dimension - N inch	0.47 in
Dimension - Outside Diameter inch	0.63
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	0.87 in
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	95 mm², 2/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)