

# YAV95M8

by Burndy  
Catalog ID: YAV95M8

Copper Tubing Terminal, 1 Hole W/insp window, 95 mm Class 2, 14 Index, 8 mm Stud



## Product Details

### General

Connector Type	Terminal - Ring
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810324141
UPC 12 Digit	7818103241411

### Dimensions

Dimension - B Length inch	0.81 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8.4
Dimension - L Length Overall mm	50.3
Dimension - Length Overall inch	1.98
Dimension - N inch	0.34
Dimension - Outside Diameter inch	0.63
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	0.87 in
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper Str Size Range	95 mm <sup>2</sup> , 2/0 AWG
-----------------------------------	------------------------------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)