



YAZ252NTC38

by Burndy
Catalog ID: YAZ252NTC38

Prop 65 Notice

Cu Tubing Hylug, 2 Holes with Inspection Window, 1/0 AWG Code, 100 Navy, 600V-35kV, 3/8" stud, Long, Compression, 0.40 in BCD, Pink

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, With Inspection Window, Tongue Angle: Straight, Wire Strip Length: 1-7/16 IN, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Die Index: 12, Color Code: Pink, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W25VT, W25RT, X25RT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W25VT, W25RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U25RT, U2CABT Die, (2), Y46 Tool, U25RT, U2CABT Die With PUADP-1 Adapter, (2), Conductor Type: Commercial Stranded Copper, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-3, MY29-11 Tool, (2), MRC840 Tool, (4)

Product Details

General

Application	For Code Conductor
Color Code	Pink
Connector Type	Terminal
Construction Material - Main	Copper tubing
Die Index	12;348
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YAZ-2TC, Code Conductor Long Barrel
UPC	781810227824
UPC 12 Digit	7818102278244

Dimensions

Dimension - B Length inch	1.38
Dimension - Bolt Size fraction	3/8
Dimension - E Spacing between Holes fraction	1-3/4
Dimension - Hole Size inch	0.4
Dimension - Hole Size mm	10
Dimension - L Length Overall mm	110

Dimension - Length Overall inch	4.35
Dimension - N inch	0.41
Dimension - Outside Diameter inch	0.51
Dimension - Pad Width inch	0.75
Dimension - Strip Length inch	1-7/16
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	100 Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)