



# YAZ254TC38E1G1

by Burndy  
Catalog ID: YAZ254TC38E1G1

Prop 65 Notice

CULUG-4HOLES-SPLIT PAD

## Product Details

### General

Color Code	Pink
Connector Type	Terminal
Die Index	12;348
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810649183
UPC 12 Digit	7818106491833

### Dimensions

Dimension - B Length inch	1.38
Dimension - Bolt Size fraction	3/8
Dimension - E Spacing between Holes fraction	1.13
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10
Dimension - L Length Overall mm	101
Dimension - Length Overall inch	3.96
Dimension - N inch	0.31
Dimension - Outside Diameter inch	0.51
Dimension - Pad Width inch	1.63
Dimension - Strip Length inch	1-7/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	100 Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)