

YAZ25TC1245

by Burndy
Catalog ID: YAZ25TC1245

Prop 65 Notice

1 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window, 1/0 AWG,
100 Navy, 1/2" stud, Pink, 12 or 348 Index



Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	12;348
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810239926
UPC 12 Digit	7818102399266

Dimensions

Dimension - B Length inch	1.38
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	1.63
Dimension - Hole Size inch	0.52
Dimension - Hole Size mm	13
Dimension - L Length Overall mm	66
Dimension - Length Overall inch	2.61
Dimension - N inch	0.53
Dimension - Outside Diameter inch	0.51
Dimension - Pad Width inch	0.75
Dimension - Strip Length inch	1-7/16
Dimension - Z inch	0.55
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	100 Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)