

YAZ262TC38E16

by Burndy
Catalog ID: YAZ262TC38E16

Prop 65 Notice

CULUG-2/0, 2 HOLE 1-3/4



Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810563472
UPC 12 Digit	7818105634722

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Hole Size mm	0.41
Dimension - L Length Overall mm	115 mm
Dimension - Length Overall inch	4.51 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-9/16
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	125 Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)