



YAZ264TC38E1G1

by Burndy
Catalog ID: YAZ264TC38E1G1

CULUG-4 HOLES-SPLIT PAD

Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810649190
UPC 12 Digit	7818106491900

Dimensions

Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.09 in
Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	3/8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

Conductor - Material	Copper
----------------------	--------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)