



YAZ294TCG1

by Burndy
Catalog ID: YAZ294TCG1

Prop 65 Notice

Cu Hylug, Split Pad, 4 Holes, W/Insp Window, 250 kcmil Code, 250 Navy, Yellow, 16 Index, 1/4 IN Bolt Size, 1-11/16 IN Strip Length

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Yes
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810636091
UPC 12 Digit	7818106360911

Dimensions

Dimension - B Length inch	1.62 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	100 mm
Dimension - Length Overall inch	3.94 in
Dimension - Pad Width inch	1.38 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	1/4
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)