



YAZ312NTCFX

by Burndy
Catalog ID: YAZ312NTCFX

Prop 65 Notice

2 Hole HULYG Cu Compr Terminal, Long Brll, W/ Insp Window, 250(637/#24) DLO, Class I, K, M, 1/2" stud, 1.75" spacing, White, 17 or 298 Index.

Features: With Inspection Window, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (3), Die Index: 18 Or 324, Color Code: Red, Conductor Type: Flexible Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W31VT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W31VT, W31RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U31RT, U29ART Die, (4), Y46 Tool, U31RT, U29ART Die With PUADP-1 Adapter, (4), Tongue Angle: Straight, Wire Strip Length: 2-1/16 IN

Product Details

General

Application	For Flex Conductors
Color Code	White
Connector Type	Terminal
Die Index	17;298
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810228609
UPC 12 Digit	7818102286099

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.02 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	143 mm

Dimension - Length Overall inch	5.64 in
Dimension - Length Side B inch	5.64 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	2-1/16
Dimension - Thread Size	1/2
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	250 (637/#24)
Conductor - Copper Flex I Size	250
Conductor - Copper Flex K Size	250
Conductor - Copper Flex M Size	250
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)