

YAZ312TC14E2FX

by Burndy
Catalog ID: YAZ312TC14E2FX

Prop 65 Notice

2 Hole HULYG Cu Compr Terminal, Long Brrl, W/ Insp Window,
250(637/#24) DLO, Class I, K, M, 1/4" stud, .75" spacing, White, 17 or 298
Index



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	17;298
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810324158
UPC 12 Digit	7818103241588

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	1.40 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.02 in
Dimension - Length Side B inch	4.02 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	2-1/16
Dimension - Thread Size	1/4 in

Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	250 (637/#24)
Conductor - Copper Flex G Size	250 kcmil
Conductor - Copper Flex G Size Range	250 kcmil
Conductor - Copper Flex H Size	250 kcmil
Conductor - Copper Flex H Size Range	250 kcmil
Conductor - Copper Flex I Size	250
Conductor - Copper Flex I Size Range	250
Conductor - Copper Flex K Size	250
Conductor - Copper Flex K Size Range	250
Conductor - Copper Flex M Size	250
Conductor - Copper Flex M Size Range	250
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)