



## YAZ312TC38FX

by Burndy  
Catalog ID: YAZ312TC38FX

Prop 65 Notice

Cu compression long barrel flex conductor, 2 holes/W/ insp window, 250 flex(637/24), Class I,K,M, 3/8" stud, Tin plated, White, 17 index

## Product Details

### General

Color Code	White
Connector Type	Terminal
Die Index	17;298
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810228586
UPC 12 Digit	7818102285866

### Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.84 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	113 mm
Dimension - Length Overall inch	4.45 in
Dimension - Length Side B inch	4.45 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	2-1/16
Dimension - Thread Size	3/8

Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	250 (637/#24)
Conductor - Copper Flex G Size	250 kcmil
Conductor - Copper Flex G Size Range	250 kcmil
Conductor - Copper Flex H Size	250 kcmil
Conductor - Copper Flex H Size Range	250 kcmil
Conductor - Copper Flex I Size	250
Conductor - Copper Flex I Size Range	250
Conductor - Copper Flex K Size	250
Conductor - Copper Flex K Size Range	250
Conductor - Copper Flex M Size	250
Conductor - Copper Flex M Size Range	250
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)