

YAZ342NT38FX

by Burndy
Catalog ID: YAZ342NT38FX

Prop 65 Notice

Cu Comp Terminal Flex Cond, Narrow Tongue/Bvl Entry, 2 Hole/W/InspWindow, 373.7 kcmil(925/#24) DLO, 350 kcmil Flex, 3/8" Stud, 1.00" Spacing , Lng bbl.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 19, Tongue Angle: Straight, Finish: Electro-Tin Plated, Wire Strip Length: 2-5/16 IN, Temperature Rating: 90 DEG C, Color Code: Blue, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W32VT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W32VT, W32RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U32RT Die, (4), Y46 Tool, U32RT Die With PUADP-1 Adapter, (4), Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Conductor Type: Flexible



Product Details

General

Application	For Flex Conductors
Color Code	Blue
Connector Type	Terminal
Die Index	19
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YAZ-2-NTFX, Long Barrel Narrow Tongue
UPC	781810166055

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Diameter Min Size inch	1.84 in
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.85 in
Dimension - Length Side B inch	4.85 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	1.06 in

Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	2-5/16
Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	373.7 (925/#24) DLO
Conductor - Copper Flex G Size	350 kcmil
Conductor - Copper Flex H Size	350 kcmil
Conductor - Copper Flex I Size	350 kcmil
Conductor - Copper Flex K Size	350 kcmil
Conductor - Copper Flex M Size	350 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)