

YAZ342TC38FXB

by Burndy
Catalog ID: YAZ342TC38FXB

Prop 65 Notice

Cu compression long barrel flex conductor, 2 holes/W/ insp window, 373.3 kcmil(925/24), 3/8" stud, Belled end, Blue, 19 index



Product Details

General

| | |
|--------------------------------------|--|
| Color Code | Blue |
| Connector Type | Terminal |
| Die Index | 19;470 |
| Feature - Barrel Style | <ul style="list-style-type: none"> Belled Skived |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive |
| UPC | 781810277164 |
| UPC 12 Digit | 7818102771644 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 2-1/2 in |
| Dimension - B Length inch | 2.48 in |
| Dimension - Hole Size inch | 0.41 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - Inside Diameter inch | 0.83 in |
| Dimension - L Length Overall mm | 129 mm |
| Dimension - Length Overall inch | 5.09 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 1.06 in |
| Dimension - Pad Width inch | 1.55 in |
| Dimension - Z inch | 0.43 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
|-------------------|-------|

Conductor Related

| | |
|--------------------------------|-----------------|
| Conductor - Copper DLO Size | 373.7 (925/#24) |
| Conductor - Copper Flex G Size | 350 |
| Conductor - Copper Flex H Size | 350 |
| Conductor - Copper Flex I Size | 350 |
| Conductor - Copper Flex K Size | 350 |
| Conductor - Copper Flex M Size | 350 |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 6 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)