



YAZ34TC3890

by Burndy
Catalog ID: YAZ34TC3890

Cu Tubing Hylug (One Hole Code); 1 Hole with Inspection Window; 500 kcmil Code; 600V-35kV; 3/8" stud; Long; Compression; 0.40 in BCD; Brown

Product Details

General

| | |
|--------------------------------------|--------------------------------|
| Color Code | Brown |
| Connector Type | Terminal |
| Die Index | 20;299 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive, Tin Plated |
| UPC | 781810240458 |
| UPC 12 Digit | 7818102404588 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 2-1/4 in |
| Dimension - B Length inch | 2.25 in |
| Dimension - Bolt Hole Size inch | 0.40 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Height inch | 3.41 in |
| Dimension - Hole Size inch | 0.40 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 39 mm |
| Dimension - Length Overall inch | 1.53 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 1.06 in |
| Dimension - Pad Width inch | 1.55 in |
| Dimension - Strip Length inch | 2-5/16 |
| Dimension - Z inch | 0.42 in |
| Physical Attribute - Tongue Angle | 90 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------|-----------|
| Conductor - Copper Str Size | 500 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)