



## YAZ392NNT90

by Burndy  
Catalog ID: YAZ392NNT90

Prop 65 Notice

2 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window, 750 kcmil,  
1/2" stud, 1.75" spacing, Black, 24 Index

## Product Details

### General

|                                      |                                |
|--------------------------------------|--------------------------------|
| Color Code                           | Black                          |
| Connector Type                       | Terminal                       |
| Die Index                            | 24                             |
| Feature - Barrel Style               | Skived                         |
| Feature - Barrel Type                | Long                           |
| Material                             | Copper                         |
| Physical Attribute - Number of Holes | 2                              |
| Physical Attribute - Tongue Type     | Standard                       |
| Plated                               | Y                              |
| Plating Type                         | Tin - Electro Plated           |
| Trade Name                           | HYLUG™                         |
| Type                                 | Long Barrel, Skive, Tin Plated |
| UPC                                  | 781810211618                   |
| UPC 12 Digit                         | 7818102116188                  |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - B Length fraction     | 2-7/8 in |
| Dimension - B Length inch         | 2.88 in  |
| Dimension - Bolt Hole Size inch   | 0.56 in  |
| Dimension - Bolt Size fraction    | 1/2      |
| Dimension - Height inch           | 4.27 in  |
| Dimension - Hole Size inch        | 0.56 in  |
| Dimension - Hole Size mm          | 14 mm    |
| Dimension - L Length Overall mm   | 98 mm    |
| Dimension - Length Overall inch   | 3.87 in  |
| Dimension - N inch                | 0.62 in  |
| Dimension - Outside Diameter inch | 1.30 in  |
| Dimension - Pad Width inch        | 1.63 in  |
| Dimension - Strip Length inch     | 2-15/16  |
| Dimension - Z inch                | 0.65 in  |

|                                   |           |
|-----------------------------------|-----------|
| Physical Attribute - Tongue Angle | 90 Degree |
|-----------------------------------|-----------|

## Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

## Conductor Related

|                             |           |
|-----------------------------|-----------|
| Conductor - Copper Str Size | 750 kcmil |
| Conductor - Material        | Copper    |

## Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 6 |
|-----------------------|---|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)