



## YAZ3C2TC38SLBOX500

by Burndy  
Catalog ID: YAZ3C2TC38SLBOX500

Prop 65 Notice

Cu Tubing Hylug Slotted; 2 Holes with Inspection Window; #3 AWG, #2 SOL Code(25mm<sup>2</sup> STR), 50 Navy; 600V-35kV; 3/8" stud; Long; Compression; 0.41 in BCD; White

### Product Details

#### General

Color Code	White
Connector Type	Terminal
Die Index	9
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810512302
UPC 12 Digit	7818105123022

#### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.38 in
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.43 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	1 5/16
Dimension - Stud Size inch	3/8
Physical Attribute - Tongue Angle	Straight

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper Str Size	3 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)