

YAZ442NNTFX

by Burndy
Catalog ID: YAZ442NNTFX

Prop 65 Notice

Hylug(Two Hole Flex), 777.7 kcmil, 7.09 in L, 1.62 in W, Tin Plated.

Features: HYLUG, 2-Hole, Narrow Tongue Copper Compression Terminal That Accommodates Flex And AWG Conductor, Temperature Rating: 90 DEG C, Conductor Type: Flexible



Product Details

General

Application	For Flex Conductors
Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Narrow Tongue
UPC	781810166147

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	3-1/16
Dimension - Stud Size inch	1/2 in
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex H Size	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)