

YAZ442NT38FX

by Burndy
Catalog ID: YAZ442NT38FX

Prop 65 Notice

Copper Compression Lug, 2 Hole w/ Inspection Window, 750 Flex, 3/8" Stud, 1" Stud Hole Spacing, Long Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, With Inspection Window, Finish: Electro-Tin Plated, Tongue Angle: Straight, Wire Strip Length: 3-1/16 IN, Temperature Rating: 90 DEG C, Color Code: Yellow, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y35, Y39, Y750, PAT750 Tool, U44XRT Die, (4), Y46 Tool, U44XRT Die With PUADP-1 Adapter, (4), Conductor Type: Flexible, Die Index: L115



Product Details

General

Application	For Flex Conductors
Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YAZ-2-NTFX, Long Barrel Narrow Tongue
UPC	781810166178

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Diameter Min Size inch	2.03 in
Dimension - L Length Overall mm	155 mm
Dimension - Length Overall inch	6.09 in
Dimension - Length Side B inch	6.08 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	3-1/16

Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex H Size	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)