



## YAZ442NTCFX

by Burndy  
Catalog ID: YAZ442NTCFX

Prop 65 Notice

2 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window, 777.7(1925/#24) DLO, 750 kcmil Flex, 1/2" stud, Yellow, L115 Index

Features: With Inspection Window, Conductor Type: Flexible Copper, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Tongue Angle: Straight

## Product Details

### General

Application	For Flex Conductors
Color Code	Yellow
Connector Type	Terminal
Construction Material - Main	Copper tubing
Die Index	L116
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Yes
Plating Type	Tin-Electro plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YAZ-2-NTFX, Long Barrel Narrow Tongue
UPC	781810228692
UPC 12 Digit	7818102286922

### Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	3-1/16

Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex H Size	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)