

YAZ47TC1245

by Burndy
Catalog ID: YAZ47TC1245

CULUG-1750KCM-LNG W/PORT



Product Details

General

| | |
|--------------------------------------|--------------------------------|
| Color Code | Gray |
| Connector Type | Terminal |
| Die Index | 33 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive, Tin Plated |
| UPC | 781810240953 |
| UPC 12 Digit | 7818102409533 |

Dimensions

| | |
|---------------------------------|-----------|
| Dimension - B Length fraction | 3-7/16 in |
| Dimension - B Length inch | 3.44 in |
| Dimension - Bolt Hole Size inch | 0.52 in |
| Dimension - Bolt Size fraction | 1/2 |
| Dimension - Height inch | 4.92 in |
| Dimension - Hole Size inch | 0.52 in |
| Dimension - Hole Size mm | 13 mm |
| Dimension - L Length Overall mm | 138 mm |
| Dimension - Length Overall inch | 5.45 in |

| | |
|-----------------------------------|-----------|
| Dimension - N inch | 0.53 in |
| Dimension - Outside Diameter inch | 1.98 in |
| Dimension - Pad Width inch | 2.90 in |
| Dimension - Strip Length inch | 3-1/2 |
| Dimension - Z inch | 0.55 in |
| Physical Attribute - Tongue Angle | 45 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------|------------|
| Conductor - Copper Str Size | 1750 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)